Telefax No.: (062) 925-1918 regionix@pca.gov.ph

Bids and Awards Committee

The Philippine Coconut Authority (PCA), through its Bids and Awards Committee (BAC), as duly authorized to conduct **Small Value Procurement (SVP)** for the items stated below, in accordance with **Section 53.9 Small Value Procurement** of the Revised Implementing Rules and Regulations of the Republic Act. No. 9184, hereby invites all interested suppliers/bidders to offer their lowest government price.

The PCA, hereinafter referred to as "the Purchaser", now requests submission of a price quotation for the subject below:

Supply and Delivery of the following: 1. Microscope Specification: Body: Aluminum die-cast metal frame, protective plastic covering Optical System: Infinity Optical System Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment for coarse adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal/ Trinocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional). Tube inclination: 309, Light path selector: None / Eyepiece/Camera Port: 100/0 or 0/100 Intervention of the property	Article and Descriptions	Quantity	Unit Price (PhP)	Approved Budget for the Contract (ABC) – (PhP)	Cost of Bid Docs (PhP)
Specification: - Body: Aluminum die-cast metal frame, protective plastic covering - Optical System: Infinity Optical System - Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal/, Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	Supply and Delivery of the following:			98,162.00	100.00
- Body: Aluminum die-cast metal frame, protective plastic covering - Optical System: Infinity Optical System - Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	1. Microscope	One (1) unit	95 000 00		
frame, protective plastic covering Optical System: Infinity Optical System Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15xEyepiece (FN): 12 (optional), Tube inclination: 309, Light path selector: None / Eyepiece/Camera Port: 100/0 or	Specification:	One (1) unit	33,000.00		
- Optical System: Infinity Optical System - Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-funga): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 309, Light path selector: None / Eyepiece/Camera Port: 100/0 or	- Body: Aluminum die-cast metal				
System - Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	frame, protective plastic covering				
- Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (MxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	- Optical System: Infinity Optical				
transmitted illumination system, LED power consumption: 0.5W (nominal value) Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	System				
power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	·				
value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	•				
- Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	· · · · · · · · · · · · · · · · · · ·				
Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	· ·				
Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	<u> </u>				
adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
(minimum adjustment gradations: 2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
2.5 um) Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
- Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or	<u> </u>				
- Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
- Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or	1				
Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
12 (optional), Tube inclination: 30º, Light path selector: None / Eyepiece/Camera Port: 100/0 or					
Light path selector: None / Eyepiece/Camera Port: 100/0 or	, , , , , , , , , , , , , , , , , , , ,				
Eyepiece/Camera Port: 100/0 or					
	•				-
U/ 100, interpupiliary distance	0/100, Interpupillary distance			2321	172

REPUBLIC OF THE PHILIPPINES

R D

DEPARTMENT OF AGRICULTURE PHILIPPINE COCONUT AUTHORITY

Regional Government Center, Brgy. Balintawak, Pagadian City, Zamboanga del Sur

Telefax No.: (062) 925-1918

regionix@pca.gov.ph

Interested suppliers are required to submit the following documents:

- 1. Valid and current Mayor's/Business Permit
- 2. PhilGEPS Registration Number
- 3. Latest Income/Business Tax Return
- 4. Omnibus Sworn Statement (attachment 2)

PCA Condition of Sale:

- 1. Delivery Schedule: 15 calendars days from the receipt of the approved PO/NTP
- 2. Bid Validity: 60 calendar days from the submission of bids
- 3. Delivery site as follows: *Philippine Coconut Authority Region IX, Regional Government Center, Barangay Balintawak, Pagadian City, Zamboanga del Sur*.

Award of contract shall be made to the bidder with the lowest quotation for the subject goods which comply with the minimum technical specifications and other terms and conditions stated herein.

Any alteration, erasures, or overwriting shall be valid only if they are signed or initialed by the bidder or his/her duly authorized representative.

A complete set of Bidding Documents may be purchased by interested Bidders on from the address below and upon payment of a non-refundable fee as indicated above, pursuant to the latest



Regional Government Center, Brgy. Balintawak, Pagadian City, Zamboanga del Sur Telefax No.: (062) 925-1918

regionix@pca.gov.ph

guidelines issued by the GPPB. It may also be downloaded free of charge from the website of PhilGEPS provided that bidders shall pay the non-refundable price.

The complete schedule of bidding activities is as follows:

Sale and Issuance of Bid Documents

- December 16 –December 22, 2022

Submission of Price Quotation

- December 23, 2022; 9:30 AM

- December 23, 2022; 10:00 AM

Submission of duly signed price quotation form (attachment 1) and eligibility documents is not later than 9:30am of December 23, 2022 at the PCA Regional Office IX, Regional Government Center, Brgy. Balintawak, Pagadian City. Open submission may be done manually, email (regionix@pca.gov.ph) or thru Facsimile No. (062) 925-1918.

The penalty for the late deliveries is one tenth (1/10) of one (1) percent of the cost of the unperformed portion for every day of delay. The maximum deduction shall be ten percent (10%) of the contract price. Once the cumulative amount of the liquidated damage reaches ten percent (10%) of the contract price, the procuring entity shall rescind the contract without prejudice to other courses of action and remedies open to it.

The PCA reserves the right to reject any and all bids, declare a failure of bidding, or not award the contract in accordance with Section 41 or RA 9184 and its IRR, without thereby incurring any liability to the affected bidder or bidders.

For further information, please refer to:

JUNRIE B. BERADIO

BAC Secretariat PCA Region IX Regional Center, Brgy. Balintawak Pagadian City, Zamboanga del Sur Mobile No. 0997-654-9395 Tel. No. (062) 925-1918 **BIHILDIS A. QUEZON**

BAC Chairwoman PCA Region IX Sta. Isabel, Dipolog City Zamboanga del Norte Tel. No. (065) 908-0922



Telefax No.: (062) 925-1918 regionix@pca.gov.ph

Attachment 1

PRICE QUOTATION FORM

The Bids and Awards Committee
Philippine Coconut Authority RIX,
Regional Government Center,
Brgy. Balintawak, Pagadian City

Date: _____

Sir/Madam:

Zamboanga del Sur

After having carefully read and accepted the terms and conditions in the Request for Quotation, hereunder is our price quotation for the item/s identified below:

ItemNo.	Article and Descriptions	Quantity	Unit Price	Total Price (VAT Inclusive)
	Supply and Delivery of the following:			
1	Microscope Specification: - Body: Aluminum die-cast metal frame, protective plastic covering - Optical System: Infinity Optical System - Illumination System: Built-in transmitted illumination system, LED power consumption: 0.5W (nominal value) - Focusing: Stage heigth movement, Coarse movement stroke: 15mm, Coarse adjustment limit stopper, Torque adjustment for coarse adjustment knob, Fine focus knob (minimum adjustment gradations: 2.5 um) - Revolving Nosepiece: Fixed quadruple nosepiece with inward tilt - Stage: Wire movement mechanical fixed stage: Size: (WxD): 174mm x 89mm, Traveling range (X x Y):76 mm x 30mm, Specimen Holder, Specimen position scale - Observation Tube: Type:Binocular & Anti-fungal/ Trinocular & Anti-fungal, Eyepiece(anti-fungal): 10X field number(FN): 20 15XEyepiece (FN): 12 (optional), Tube inclination: 30°, Light path selector: None / Eyepiece/Camera	One (1) unit	P	P
	Port: 100/0 or 0/100, Interpupillary			

REPUBLIC OF THE PHILIPPINES

DEPARTMENT OF AGRICULTURE

PHILIPPINE COCONUT AUTHORITY
Regional Government Center, Brgy. Balintawak, Pagadian City, Zamboanga del Sur Telefax No.: (062) 925-1918

regionix@pca.gov.ph

	distance adjusting range: 48-75 mm, Eyepoint adjustment: 370.0-432.9mm Condenser: Abbe condenser NA 1.25 with oil immersion, Built-in aperture iris diaphragm Objectives: Plan Achromat, Anti-fungal: 4X NA0.1 W.D.27.8MM, 10X NA0.25 W.D.8.0MM, 20X NA0.4 W.D.2.5MM(optional), 40X NA0.65 W.D. 0.6MM, 100XOil NA1.25 W.D.0.13m Optional Accessories: Reflection mirror(CH20-MM), eyepiece micrometer, Dust cover, darkfield stop (CH2-DS+CH2-FH), Field Diaphragm (CX23-FS)*, Dedicated wooden case (CH20-WB2) Dimensions (WxDxH): 198mm x 398mm x 386mm/ 198mm x 398mm x 430mm Weight: Approximately 5.9kg / Approximately 6.5 kg Rated Voltage/Electric Current: AC 100- 240V 50/60Hz 0.4A Power Consupmption: Less than 2 W	One		
2	Rubber Bulb (Syringe Medical)	Hundred Two (102) pcs	P	P

AMOUNT IN WORD	S:
The above-quoted p	orice is inclusive of all costs and applicable taxes.
Very truly yours,	
AUTHORIZED REPR	ESENTATIVE:
Signature Printed Name Company Name	:
Contact No	:



Regional Government Center, Brgy. Balintawak, Pagadian City, Zamboanga del Sur Telefax No.: (062) 925-1918

regionix@pca.gov.ph

Omnibus Sworn Statement

REPUBLIC OF THE PHILIPPINES)
CITY/MUNICIPALITY OF) S.S

AFFIDAVIT

I, [Name of Affiant], of legal age, [Civil Status], [Nationality], and residing at [Address of Affiant], after having been duly sworn in accordance with law, do hereby depose and state that:

1. Select one, delete the other:

If a sole proprietorship: I am the sole proprietor of [Name of Bidder] with office address at [address of Bidder];

If a partnership, corporation, cooperative, or joint venture: I am the duly authorized and designated representative of [Name of Bidder] with office address at [address of Bidder];

2. Select one, delete the other:

If a sole proprietorship: As the owner and sole proprietor of [Name of Bidder], I have full power and authority to do, execute and perform any and all acts necessary to represent it in the bidding for [Name of the Project] of the [Name of the Procuring Entity];

If a partnership, corporation, cooperative, or joint venture: I am granted full power and authority to do, execute and perform any and all acts necessary and/or to represent the [Name of Bidder] in the bidding as shown in the attached [state title of attached document showing proof of authorization (e.g., duly notarized Secretary's Certificate issued by the corporation or the members of the joint venture)];

- 3. [Name of Bidder] is not "blacklisted" or barred from bidding by the Government of the Philippines or any of its agencies, offices, corporations, or Local Government Units, foreign government/foreign or international financing institution whose blacklisting rules have been recognized by the Government Procurement Policy Board;
- 4. Each of the documents submitted in satisfaction of the bidding requirements is an authentic copy of the original, complete, and all statements and information provided therein are true and correct;
- 5. [Name of Bidder] is authorizing the Head of the Procuring Entity or its duly authorized representative(s) to verify all the documents submitted;
- 6. The owner or sole proprietor is not related to the Head of the Procuring Entity, members of the Bids and Awards Committee (BAC), the Technical Working Group, and the BAC Secretariat, the head of the Project Management Office or the end-user unit, and the project consultants by consanguinity or affinity up to the third civil degree;
- 7. [Name of Bidder] complies with existing labor laws and standards; and
- 8. *[Name of Bidder]* is aware of and has undertaken the responsibilities as a Bidder in

"A food-secure Philippines with prosperous farmers and fisherfolk"

REPUBLIC OF THE PHILIPPINES DEPARTMENT OF AGRICULTURE PHILIPPINE COCONUT AUTHORITY Pegianal Government Center, Broy, Balintawak, Pagadian

Regional Government Center, Brgy. Balintawak, Pagadian City, Zamboanga del Sur Telefax No.: (062) 925-1918

regionix@pca.gov.ph

compliance with the Philippine Bidding Documents, which includes:

- a. Carefully examining all of the Bidding Documents;
- b. Acknowledging all conditions, local or otherwise, affecting the implementation of the Contract;
- c. Making an estimate of the facilities available and needed for the contract to be bid, if any; and
- d. Inquiring or securing Supplemental/Bid Bulletin(s) issued for the [Name of the Project].
- 9. [Name of Bidder] did not give or pay directly or indirectly, any commission, amount, fee, or any form of consideration, pecuniary or otherwise, to any person or official, personnel or representative of the government in relation to any procurement project or activity.
- 10. In case advance payment was made or given, failure to perform or deliver any of the obligations and undertakings in the contract shall be sufficient grounds to constitute criminal liability for Swindling (Estafa) or the commission of fraud with unfaithfulness or abuse of confidence through misappropriating or converting any payment received by a person or entity under an obligation involving the duty to deliver certain goods or services, to the prejudice of the public and the government of the Philippines pursuant to Article 315 of Act No. 3815 s. 1930, as amended, or the Revised Penal Code.

IN WITNESS WHEREOF, I have hereunto set my Philippines.	y hand this day of, 20 at
	Bidder's Representative/Authorized Signatory
Doc. No. Page No. Book No. Series of 20	

